



ATTUNE AZUL/ VIOLETA CONFIGURACIÓN

LASER AZUL



BL1	BL2	BL3
FITC	PE	PE-Cy5
AF 488	PI	PE-Cy5.5
BB 515	YFP	PerCp
GFP		PerCp-Cy5.5
CSFE		7AAD

LASER VIOLETA



VL1	VL2	VL3
VB 421	VB 510	PACIFIC ORANGE
PACIFIC BLUE	AmCyan	QDOT 605
DAPI	V500c	VB 605
AF 405		eFLUOR 605NC
HORIZON V450		

HOECHST 33242		
---------------	--	--