



ATTUNE NEXT CONFIGURACIÓN

LASER VIOLETA



VL1	VL2	VL3	VL4
VB 421	VB 510	PACIFIC ORANGE	QDOT 705
PACIFIC BLUE	AmCyan	QDOT 605	VB 711
DAPI	HORIZON V500	VB 605	
AF 405	PACIFIC GREEN	eFLUOR 605NC	
HORIZON V450			
HOECHST 33242			


LASER AZUL



BL1	BL2	BL3
FITC		PerCp
AF 488	No usar este canal.	PerCp-Cy5.5
BB 515	En su lugar usar YL1.	
GFP		


CSFE

LASER AMARILLO



YL1	YL2	YL3	YL4
PE	PE-Texas Red	PE-Cy5	PE-Cy7
PI	PE-CF594	PE-Cy5.5	PE-AF750
YFP	RFP	7AAD	QDOT 800
	mCherry	QDOT 705	
	DsRed		
	PE-AF610		

LASER ROJO



RL1	RL2	RL3
APC	AF 700	APC-Cy7
AF 647	APC-AF 700	APC-H7

QDOT 655

QDOT 705

APC-AF 750