



CYTOFLEX S CONFIGURACIÓN

LASER CERCANO ULTRAVIOLETA




FL12	FL13
DAPI	HOECHST RED
HOECHST 33242	BV661

LASER VIOLETA




FL9	FL10	FL11
VB 421	VB 510	PACIFIC ORANGE
PACIFIC BLUE	AmCyan	QDOT 605
AF 405	HORIZON V500	VB 605
HORIZON V450	PACIFIC GREEN	eFLUOR 605NC

LASER AZUL



FL1	FL2	FL3	FL4	FL5
FITC	PE	PE-Texas Red	PE-Cy5	PE-Cy7
AF 488	IP	PE-CF594	PE-Cy5.5	PE-AF750
BB 515	YFP	RFP	7AAD	QDOT 800
GFP		mCherry	QDOT 705	
CSFE		DsRed		

LASER ROJO



FL6	FL7	FL8
APC	AF 700	APC-Cy7
AF 647	APC-AF 700	APC-H7
QDOT 655	QDOT 705	APC-AF 750

